

Type 2030 Series Digital Sanitary Gauge



At last, a multi-functional sanitary gauge from the experts in pressure measurement.

The new Ashcroft® sanitary digital gauge saves money, time and space. Now, one digital pressure gauge can replace three instruments... a mechanical pressure gauge, a transducer and a switch! Save space, installation costs and the cost of additional instruments and pipe cut-outs.


Industry Leading Features Include:

- 4/20 mA Output
- (1) or (2) SPDT Switches
- .25% F.S. Terminal Point Accuracy (.13 BFSL)
- IP 65 Weatherproof Case Suitable For Wash Downs
- Extra Large Display
- Easy-to-Use Password Protected Menu With:
- 5 Backlite Display Options
- 12 Engineering Units
- Menu Configure Feature
- Update Rate
- Dampen Rate
- Auto-Off
- Material Traceability Certification to EN 10204: 2004 3.1

The new Ashcroft® sanitary digital gauge has been designed to monitor pressures in critical pharmaceutical, biotech or food processing applications when a Tri-Clamp® type of connection is required. These gauges can be cleaned and steamed in place (CIP/SIP) and meet ASME B40.7. When there are requirements for a remote-mount digital sanitary gauge and temperature error is a concern, the unique Ashcroft Type 2030 series is offered with an optional remote-mount design. This unique design eliminates additional temperature error caused by conventional capillary between the gauge and seal. These digital sanitary gauges come standard with material traceability certification to EN 10204: 2004 3.1*

Tri-Clamp® is a registered trademark of Alfa Laval Inc. *excludes 2036 series

Actual
Material Certificates
and Certificate of Conformance
supplied as standard to
EN 10204:2004 3.1







Type 2030 Series Digital Sanitary Gauge

DIMENSIONS


Types 2032, 2132 or 2232 with 11/2" or 2" diameter seal




Types 2136 or 2236 with remote seal (XRE variation)




Types 2132 or 2232 with remote seal (XRE variation)



Types 2036 with 11/2" inline seal



Types 2136, 2236 with 11/2" inline seal



RANGES

psi	in.Hg@ (vacuum)	Comp.(4) (psi)	mmHg (pressure)	in.Hg (pressure)	in. H₂O	mBar	ft. H₂O	mPa	kPa	Bar/ KSC
15	30	-15/0/15	800	30	400	1000	60	1	100	1
30		-15/0/30	1000	60	800	1500	160	1.6	160	1.6
60		-15/0/60	2000	100	1000	2000	200	2.5	250	2.5
100		-15/0/100	3000	160		2500	300	4	400	4
160			5000	200		4000	400	6	600	6
200			10,000	300		5000	600	10	1000	10
300				400		6000	1000	16	1600	16
600				600		10,000		25	2500	25
800				800		15,000		40	4000	40
1000						20,000		60	6000	60



Type 2030 Series Digital Sanitary Gauge

SPECIFICATIONS					
Туре	Conventional Tri-Clamp®: 2032 (battery), 2132 ⁽¹⁾ (4-20mA), 2232 ⁽¹⁾ (line) In-line Tri-Clamp®: 2036 (battery), 2136 (4-20mA), 2236 (line)				
Accuracy: Terminal Point	, , , , , , , , , , , , , , , , , , ,				
Full Scale	.25% F.S. Accuracy:				
Case Size	3″				
Case Material/Finish	(3') 300 Series SS, Electropolished				
Case Enclosure Rating	Weatherproof, IP65, NEMA 4				
Wetted Parts	316 SS				
Fill Fluid	Glycerine-standard, Silicone-optional, Food grade Mineral Oil-optional				
Tri-Clamp Connection	Direct, in-line 1½", 2", Ashcroft remote in-line (XRE),				
Seal Surface Finish	12-20Ra				
Connection Location	Lower				
Ranges	15 psi thru 1,000 psi including metric, compound & vac				
Process Temp. Limits(2)	14°F / 275°F (–10°C / 135°C) to withstand clean in place (CIP) & steam in place (SIP)				
Ambient Temp.Limits(3)	14°F / 140°F (-10°C / 60°C)				
Temperature Error	±.22% per 10°F, (12°F) (Span and Zero shift can be eliminated by rezeroing the gauge at operating temperatures. <i>Temperatures</i> must be within process temperature limits)				
Storage Temperature	–4°F / 158°F (−20°C / 70°C)				
Overrange Pressure DISPLAY	2x range of gauge				
Туре	LCD				
Display Digits	5 Digits				
Character Height	.60″				
Backlite	Off By Default				
Bar Graph	Yes				
Battery Life	1000 Hrs., Battery Life Indicator - standard				
Agency Approvals	CE (excludes XRE variation)				
	Material Traceability Certification to EN 10204: 2004 3.1 standard				
KEYPAD FUNCTION					
On/Off	Manually Turns Unit On & Off (auto off options in menu)				
Zero/Clear	Zeros Display or Clears Min/Max Values When Displayed				
Min/Max Arrow Key	Stores Min & Max Values, Arrow Key allows for scrolling thru Menu items				
Menu	Allows for changes to default settings (See Below)				
Backlite (optional) Arrow Key	Manually Turns Backlite On & Off (auto off options in menu), Arrow Key allows for scrolling thru Menu items				
Enter	Selects Items In the Menu				
MENU MODE					
Engineering Units (Units)	Allows Scrolling Through Menu To Select Available Options 10 units of measurement are available psi, in. H ₂ O with 3 temp. options: 20°C, 60°F, 4°C*, mmHg, ft. H ₂ O, mPa, kPa, kg/cm _z & bar				
Configuration Mode(Config)	Allows for changes to default settings of gauge				
Bar Graph (Graph)	Allows for adjustment of bargraph & 4-20(optional feature)				
Auto Off (Off)	Allows for changes to auto off of gauge 5 Options:, 30 Min., 10 Min., 5 Min., 2 Min., Never				
Update Rate (Update)	4 Options: 100mili-sec, 1sec, 500mili-sec, 200mili-sec,				
Dampening (Damp)	6 Options: None, Average 8, 6, 4, 2 times per 100ms				
Backlite Lit (optional)	5 options: NEVER, 10 sec, 30, sec, 1 min, 5 min.				
Zero Disable	Zero "lockout" feature				
Field Recalibration	Zero, Span & Midscale (password protected)				
0 - 111 12	Aller of Grand Phanes of Grand Organia				

Allows for recalibration of zero & span

(includes factory default calibration)					
OPTIONS					
Description	Code	Case Size			
Case Options					
Front Flange (Brushed SS case standard)	FF				
Fill Options					
Food grade mineral oil Silicone Dow Corning 200 food grade silicone	MY CX CZ				
Switch Options					
(1) SPDT Switch (12-36Vdc)	U1	3″			
(2) SPDT Switch (12-36Vdc)	U2	3″			
Line Power with 4-20mA output (Line power (Type 2274) required for switching options.) (Terminal blocks standard with 4½" case.) (Flying leads standard with 3")	AO	3″			
Wiring Options 3 Shielded cable standard					
Keypad Options					
Backlite	BL				
Miscellaneous Options					
Battery Backup (Battery standard with Type 2074) (Available with Types 2174 & 2274)	BK				
Protective Front Cover	PP	3″ only			
Remote Mounted Seal	RE	Std. w/3 shielded cable			

Notes (1)3 shielded cable standard

- (2) Rezero gauge often after exposure to elevated temperatures and use.
- (3) The 2030 Series Digital Gauge is not suitable for an autoclave.
- (4) Vacuum and compound pressure ranges require food grade mineral oil fluid option (MY).

Calibration